



The compressor can be installed on any level floor capable of supporting it. A dry, well ventilated area where the atmosphere is clean is recommended. A minimum of 700mm at the rear, the top and all sides of the machine is recommended for adequate service access and ventilation.

Adequate clearance needs to be allowed around and above the machine to permit safe access for specified maintenance tasks.

External piping shall not exert any unresolved moments or forces on the unit. Use pipe size as large or larger at discharge connection.

	NAME	DATE		~			
DRAWN	ΣK	14/10/15	© S Deno Compressors				
CHECKED							
ENG APPR			SCREW COMPRESSOR DSR 15/18/22				
MGR APPR			SEINEW COLITICESSUIT BSIT 15/10/22				
DENO Compressors B.V. Van der Giessenweg 49			SIZE A3	SUBJECT: GENERAL ARRANGEMENT REV			
2921 LP Krimpen aan den IJssel The Netherlands info⊘denoromnal		FILE I	FILE NAME: GA DSR 15-18-22 Air Cooled-CK-rev0.dft				
		SCALE	: 1:25	WEIGHT:	SHFFT 1 OF 1		