


The compressor can be installed on any level floor capable of supporting it. A dry, well ventilated area where the atmosphere is clean is recommended. A minimum of 600mm at the rear, the top and all sides of the machine is recommended for adequate service access and ventilation.

Adequate clearance needs to be allowed around and above the machine to permit safe access for specified maintenance tasks.

External piping shall not exert any unresolved moments or forces on the unit. Use pipe size as large or larger at discharge connection.

	NAME	DATE			
DRAWN	CK	14/10/15			SCREW COMPRESSOR DSR 5/7/11
CHECKED					
ENG APPR					
MGR APPR					
DENO Compressors B.V. Van der Giessenweg 49 2921 LP Krimpen aan den IJssel The Netherlands info@denocomp.nl			SIZE A3	SUBJECT: GENERAL ARRANGEMENT	REV
			FILE NAME: GA DSR 5-7-11 Air Cooled-CK-rev0.dft		
			SCALE: 1:25	WEIGHT:	SHEET 1 OF 1